

New Manual Clamps with Front Mount Base

DESTACO is expanding the horizontal and vertical hold down clamp range with a front mount base. These variants enable applications to be highly flexible in terms of installation.



Product Highlights/Options

- Manual clamp with front mounting base
- 4 models available
- Vertical or horizontal handle action
- Extremely compact and space-saving














CLAMPING




HOLD DOWN

Features, Markets and Applications

 <p>PERFORMANCE</p>	<ul style="list-style-type: none"> • No interference with mounting connection • Hardened bushings at key pivot points • Low profile (225-UF and 235-UF) 	 <p>INDUSTRIAL</p>	 <p>ASSEMBLY</p>
 <p>SAFETY</p>	<ul style="list-style-type: none"> • Large hand clearance for improved safety (2002-UF and 2007-UF) 	 <p>AEROSPACE</p>	 <p>WELDING</p>
 <p>INTERCHANGEABLE</p>	<ul style="list-style-type: none"> • Offers the same spindles and bolt retainers within existing model group • Uses same hole pattern as existing models 	 <p>CONSUMER GOODS</p>	 <p>FIXTURE/TESTING</p>
		 <p>AUTOMOTIVE</p>	 <p>CNC/MACHINING</p>


NEW Vertical Hold Down Clamps with Front Mount Base



Space saving, compact front mount base.

Model	Max. Holding Capacity	Clamp Bar Opening (+10°)	Handle Opening (+10°)	Weight (± 10% Max)	Accessories (Supplied)	
					Spindle Assembly	Flanged Washers
2002-UF	2700 N [600 lbf]	75°	66°	0,30 kg [0.66 lb]	215208-M	215105
2007-UF	4450 N [1000 lbf]	76°	64°	0,71 kg [1.57 lb]	2007208-M	507107

NEW Horizontal Hold Down Clamps with Front Mount Base



Space saving, compact front mount base.

Model	Max. Holding Capacity	Clamp Bar Opening (+10°)	Handle Opening (+10°)	Weight (± 10% Max)	Accessories (Supplied)	
					Spindle Assembly	Flanged Washers
225-UF	2220 N [500 lbf]	92°	70°	0,32 kg [0.70 lb]	215208-M	215105
235-UF	3340 N [750 lbf]			0,92 kg [2.03 lb]	2007208-M	507107

Dimensions and technical information are subject to change without notice.

MC_UFMC-F_0122_US

CORPORATE HEADQUARTERS
US
+1-888-DESTACO
+1-248-836-6700
northamerica@destaco.com

DE
+49-6171-705-0
europe@destaco.com
PL
+48-506002115
poland@destaco.com

FR
+33-4-7354-5001
france@destaco.com
NL
+31-297285332
benelux@destaco.com

UK
+44-1902-797980
uk@destaco.com
CZ
+420-603-577-341
czech@destaco.com

SP
+34-936361680
spain@destaco.com
IN
+91-80-41123421-426
india@destaco.com

CN
+86-21-6081-2888
china@destaco.com
SG
singapore@destaco.com

TH
+66-2-326-0812
asia@destaco.com
CA
canada@destaco.com

MX
mexico@destaco.com