

Evolution in Productivity




92W Series Electric Power Clamps

DESTACO now offers an electrified versions of its pneumatic power clamps. The new 92W series electric power clamps will be offered in two sizes, a compact and heavy-duty version. The 92W offers adjustable speed, torque, and opening angles from the control module, with a total clamp movement of 360deg, or up-to-225 degrees with standard clamp arms installed. They also features integrated tolerance compensation that allows for part sheet thickness variations.

Leading the way into the future, our growing BIW product line of smart, electric products eliminate CO₂ use, provide important data and control for optimizing efficiencies, and are a frontrunner for flexible manufacturing with Plug & Play solutions.

As production requirements evolve, DESTACO will continue to expand our product portfolio of electric solutions for use in all types of manufacturing processes.














Product Highlights/Options

- Plug & Play solution
- Integrated part present control
- Energy efficiency - CO₂ reduction
- Self adjustment - no shims needed



Features, Markets and Applications

 ELECTRIC	<ul style="list-style-type: none"> • Daisy chain connection requires less cables • Two control and drive options available • Fast start up during installation 	 AUTOMOTIVE	 ASSEMBLY
 PERFORMANCE	<ul style="list-style-type: none"> • Controlled motion provides smooth opening and closing • Infinite clamp opening positions for multiple applications • Adjustable speed offers cycle time optimization 	 INDUSTRIAL	 WELDING
 LOW/NO MAINTENANCE	<ul style="list-style-type: none"> • Predictive maintenance for improved production planning • Provides quick restart after emergency stop 	 AEROSTRUCTURE	 FIXTURE/TESTING
		 FOOD & PACKAGING	 HARSH ENVIRONMENT

92W SERIES

Electric Smart Power Clamps | Features and Options

The **92W Series Electric Smart Clamp** are used in any applications where it is necessary to accurately position parts and tooling for the next process including assembly and welding applications.

Adjustable clamp arm swing

Adjustable opening speed

Intergrated position and hold down control

Consistent mounting pattern

Intergrated part present control

Allows the use of standard u-shape and lateral clamp arms




Two Sizes:
Compact and Heavy-Duty

Two control and drive options
available (400V and 48V)
Can be rotated in 90° increments

Part Present Control and Tolerance Compensation


The 92W Series electric power clamps has built in part present control to improve the process quality by detecting sheet metal parts during production. (No external sensors needed)

The self-adjustment function allows tolerance compensation for maximum flexibility during production. (No shims needed)



Infinite Clamp Opening Positions for Multiple Applications

Clamping can be started at any angle and can be set for any opening angle, with a total opening angle of 225° when standard clamp arm is installed.



The 92W series shares the same mounting pattern as the pneumatic versions of our power clamps:



92W
Compact

82M
40mm



92W
HD

82M
50mm

82M
63mm

Body-in-White Product Portfolio




92W Electric Power Clamp (Compact)




92W Electric Power Clamp (Heavy Duty)



98W Electric Pivot Unit (With Decentralized Drives)



92P Electric Centering Pin Clamp




96W Electric Pin Package



95W Electric Guide/Lifter



99W Electric Positional Slide



Contact DESTACO to learn more about our Electric Solutions and how we are evolving our customers' productivity in manufacturing.

Dimensions and technical information are subject to change without notice.

PC_92W-4F_0224_US

CORPORATE HEADQUARTERS
US
+1-888-DESTACO
+1-248-836-6700
northamerica@destaco.com

DE
+49-6171-705-0
europe@destaco.com
PL
+48-506002115
poland@destaco.com

FR
+33-4-7354-5001
france@destaco.com
NL
+31-297285332
benelux@destaco.com

UK
+44-1902-797980
uk@destaco.com
CZ
+420-603-577-341
czech@destaco.com

SP
+34-936361680
spain@destaco.com
IN
+91-80-41123421-426
india@destaco.com

CN
+86-21-6081-2888
china@destaco.com
SG
singapore@destaco.com

TH
+66-2-326-0812
asia@destaco.com
CA
canada@destaco.com

MX
mexico@destaco.com