

CONVEYOR APPLICATION REQUEST FORM



A DODGE COMPANY

Automation
Robohead FERGUSON
CAMCO

DATE: _____
 CONTACT NAME: _____
 COMPANY: _____
 ADDRESS: _____

PHONE: _____
 FAX: _____
 E-MAIL: _____
 REP: _____

APPLICATION INFORMATION

ENVIRONMENT: _____
 PART MATERIAL: _____
 PART DIMENSIONS: LENGTH: _____
 WIDTH: _____
 HEIGHT: _____

CONVEYOR INFO

TYPE-BELT, ROLLER, CHAIN, PLASTIC, _____
 TIMING, MAGNETIC, VACUUM _____
 TRANSFER NOSE REQUIRED: _____
 CONVEYOR LENGTH: _____ FT/MM
 CONVEYOR WIDTH: _____ IN/MM
 DRIVE TYPE: CENTER END DIRECT SIDE
 MAX. LOAD: _____ LB
 CONVEYOR MODE: ACCUMULATING CONVEYING START/STOP BELT PREFERENCE: _____

ELECTRICAL INFO

MAX. SPEED: _____ FT/MIN PHASE: SINGLE 3 PHASE
 MIN. SPEED: _____ FT/MIN SPEED: VARIABLE FIXED
 INPUT VOLTAGE: 115 VAC 230 VAC
 460 VAC 575 VAC

SIDE RAILS

SIDE RAIL TYPE: FIXED ADJUSTABLE SIDE RAIL INFO: _____

STANDS

FIXED ADJUSTABLE

STAND HEIGHT: _____
 STAND INFO: _____
 COMMENTS: _____

DRAWING APPLICATION: